

Lunettes de Protection Laser de Confort LS19, Tempe Réglable



Stock #17-639 3-4 JOURS



1



€272,00

AJOUTER AU PANIER

Qté 1-5

€272,00

Qté 6+

€244,80

Prix sur Quantité

[Demande de Devis](#)

⚠ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Couleur:
Grey

Densité Optique OD:
>5 @ 1025 - 1075nm
>6 @ 1035 - 1070nm
>7 @ 1045 - 1065nm

>2 @ 1450 - 1650nm
>3 @ 1651 - 1775nm
>4 @ 1776 - 3000nm
>5 @ 1980 - 2550nm
>5 @ 5200 - 11,000nm
>6 @ 9000 - 10,600nm

Transmission de la Lumière Visible VLT (%):
23

Certification EN 207/208:
DIRMLB5 @ 1025 - 1075nm, DIRMLB6 @ 1035 - 1070nm, D LB6 and IR LB7 and MLB7Y @ 1045 - 1065nm, DIR LB2 @ 1450 - 1650nm, DI LB3 and R LB3Y @ 1651 - 1775nm, DI LB4 and R LB3Y @ 1776 - 3000nm & 5200 - 11,000nm

Matière du Filtre:
Polymer

Filter:
LS19

Style:
Adjustable Temples Wrap Around

Conformité réglementaire

RoHS 2015:
[Conforme](#)

Certificate of Conformance:
[Visionner](#)