




NOTES:

1. SUBSTRATE
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
 T(AVG) >85% @ 390 - 485nm
 T(AVG) <1.0% @ 525 - 750nm
 T(ABS) >80% @ 400 - 485nm
 T(ABS) <1.0% @ 620 - 690nm

3. CUT AND SEAM

4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

| | S1 | S2 |
|-----------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 80-50 | 80-50 |
| CLEAR APERTURE | ≥85 % | ≥85 % |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |



| | | | |
|--------|-----------------------------|-------|--------|
| TITLE | 50 x 50 BLUE DICHOIC FILTER | | |
| DWG NO | 30635 | SHEET | 1 OF 1 |