NOTES:


1. SUBSTRATE: FUSED SILICA


2. RoHS: COMPLIANT

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN

4. COATING (APPLY ACROSS COATING APERTURE) \$1& \$2: R(ABS) ≤1.0% FROM 350 - 450nm R(AVG) ≤1.5% FROM 250 - 700nm







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	\$1 PLANO	\$2 PLANO			BI	Edmund Option	CS®
SURFACE ACCURACY SURFACE QUALITY	1λ 60-40	1λ 60-40	THIRD ANGLE PROJECTION		TITLE	25 x 25mm UV-VIS COATED, 1λ FUSED SILICA WINDOW	
CLEAR APERTURE	22.50 x 22.50	22.50 x 22.50		_			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	84476	SHEET 1 OF 1

