



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY  
DIMENSIONS ARE IN mm [INCHES]

NOTES:

- 1. OPTIONAL RECESSED SET SCREW INCLUDED
- 2. APERTURE DIAMETER: 0.8 - 20mm
- 3. MAXIMUM OPTIC EDGE THICKNESS: 11mm

TITLE	EMPTY C-MOUNT BARREL FOR Ø 25mm ACHROMAT PAIRS			
DWG NO	87184	MATERIAL	BLACK ANODIZED ALUMINUM	SHEET 1 OF 1
				REV 000