



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES




45346
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 26.341
GD RADIUS : 64.229
SCALE BAR : 200

REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

45346
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 71.9225 μm
DIFFRACTION LIMITED RANGE: 4.065 μm
PUPIL ZONE: 0.0000


EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



45346
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

45346
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE



EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM