





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. 001 | S1 | S2 |
|--------------------------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SPECTRAL TRANSMITTANCE $t_p(\%)$ | 96 | 96 |
| PASSBAND LIMIT $1 \lambda_{p1}$ (nm) | 750 | 750 |
| CUT-OFF POSITION λ_c (nm) | 665 ± 6 | 665 ± 6 |
| STOPBAND LIMIT λ_s (nm) | 580 | 580 |
| WAVELENGTH | VIS | VIS |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |



THIRD ANGLE
PROJECTION



TITLE

$\varnothing 25.4\text{mm}$, SCHOTT RG-665 LONGPASS FILTER

ALL DIMS IN

mm

DWG NO

45070

SHEET
1 OF 1