



NOTES:

- 1. SUBSTRATE
UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
HARD COATED
PERFORMANCE SPECS:
T(AVG) = 90% FROM 515 - 850nm @ 45 ° AOI
R(AVG) = 98% FROM 350 - 488nm @ 45 ° AOI
T(ABS) = 50% @ 510nm @ 45 ° AOI


3. FINE GRIND SURFACE

- 4. SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 5. TRANSMITTED WAVEFRONT DISTORTION RMS @ 632.8nm ≤1λ
- 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	22.00 x 32.00	22.00 x 32.00	TITLE			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	86332
					SHEET 1 OF 1	