## NOTES:

1. SUBSTRATE MATERIAL: N-BK7


- 2. ROHS COMPLIANT
- 3. SURFACE \$1 TO BE PARALLEL TO SURFACE \$2 TO WITHIN ≤ 3 ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)

\$1: 80% R ±5% @ 550nm 20% T ±5% @ 550nm


S2: AR R(avg) ≤1%, R(abs) ≤2% @ 400 - 700nm



CUT WITH 0.25mm MAXIMUM EDGE CHIP



ALL DIMS IN



## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

68429

SHEET 1 OF 1

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
ANGLE OF INCIDENCE	45°	45°
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm

			Edmund Optics®
	THIRD ANGLE PROJECTION	TITLE	50 x 50mm, 80 R/20 T, PLATE BEAMSPLITTER

DWG NO