


NOTES:

1. SUBSTRATE MATERIAL:
BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
4.

FINE GROUND SURFACE
5. ROHS COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A		S1	S2	DIMENSIONS ARE FOR REFERENCE ONLY				
SHAPE		CONCAVE	PLANO	<div><div><div><div></div><div></div></div><div><div></div><div></div></div></div><div><div></div><div></div></div><div>Edmund Optics®</div></div>				
EFFECTIVE FOCAL LENGTH		50.8mm	N/A					
FOCAL LENGTH TOLERANCE		±2%	N/A					
APERTURE		f/1	N/A					
SURFACE QUALITY		60-40	60-40	<div>THIRD ANGLE PROJECTION</div> <div></div>	TITLE		Ø2in, 2in FL UNCOATED, SPHERICAL MIRROR	
SURFACE FLATNESS		λ/4	λ/4					
BEVEL		PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	32811	SHEET 1 OF 1