NOTES:


1. SUBSTRATE:


PET


2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Ravg <1% @450 - 650nm **S2: CLEAR HARD COATED**

3. Rohs Compliant







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

	\$1	S2			
SHAPE	PLANO	PLANO			
WAVELENGTH RANGE	450 - 650nm	450 - 650nm			
SURFACE RESISTIVITY (Ω/Sq)	8	8			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

				Edmund Option	S®
THIRD ANGLE TITLE 1" x 1", ITO COATED EMI SHIEL WINDOW		1" x 1", ITO COATED EMI SHIELDED PLA WINDOW	STIC		
_	ALL DIMS IN	mm	DWG NO	02740	SHEET

83742

DWG NO