

NOTES:

1. SUBSTRATE MATERIAL:  
N-BK7


2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: NONE  
S2: NONE

3.  ARROW POINTS TOWARDS TILTED SURFACE

4.  FINE GROUND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

6. RoHS COMPLIANT




SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
RADIUS	∞	∞
MIN CLEAR APERTURE	Ø11.25	Ø11.25
SURFACE QUALITY	20-10	20-10
SURFACE ACCURACY	λ/10	λ/10
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm



TITLE

12.5mm N-BK7 WEDGED WINDOW

DWG NO

34244

SHEET  
1 OF 1