NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 30% R ±5% @ 550nm 70% T ±5% @ 550nm

S2: AR ¹/₄λ MgF2 @ 550nm







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHEET 1 OF 1

REV. A	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	80-50	80-50	
SURFACE FLATNESS	4 - 6λ	4 - 6λ	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	

			Edmund Option	S®
HIRD ANGLE _ ROJECTION	$\phi \Leftrightarrow$	TITLE	75 x 75mm, 30 R/70 T, PLATE BEAMSPLI	TTER
all DIMS IN	mm	DWG NO	46640	SHEET 1 OF