## NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

\$1: 30% R ±5% @ 550nm 70% T ±5% @ 550nm

S2: AR <sup>1</sup>/<sub>4</sub>λ MgF2 @ 550nm

4. EDGES CUT





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

	THIRD ANGLE PROJECTION	$\phi \Leftrightarrow$	TITLE
_	ALL DIMS IN	mm	DWG

	Edmund Optics®
TITLE	Ø12.5mm, 30 R/70 T, PLATE BEAMSPLITTER

l DIMS IN	mm	DWG NO	45312	SHEET 1 OF 1