




NOTES:

- 1. SUBSTRATE
YVO4
- 2. EXTINCTION RATIO: >200,000:1
- 3. BEAM DEVIATION: <3 ARCMIN
- 4. DAMAGE THRESHOLD,
PULSED: 10J/cm² @ 1064nm, 20ns
- 5. RoHS NOT COMPLIANT


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



| | |
|------------------|--------------|
| CLEAR APERTURE | Ø10 |
| SURFACE QUALITY | 20-10 |
| WAVELENGTH RANGE | 400 - 4000nm |

| | |
|---|----|
| THIRD ANGLE PROJECTION  | |
| ALL DIMS IN | mm |

| | | | |
|--------|--------------------------|-----------------|--|
| TITLE | YVO4 WOLLASTON POLARIZER | | |
| DWG NO | 68822 | SHEET 1 OF 1 | |