




NOTES:

- 1. SUBSTRATE
A-BBO
- 2. EXTINCTION RATIO: >200,000:1
- 3. BEAM DEVIATION: <3 ARCMIN
- 4. BEAM SEPARATION (°): 8.0 - 14.0 , 8 @ 800nm
- 5. DAMAGE THRESHOLD,
CW: > 500 MW/cm²
- 6. RoHS NOT COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



CLEAR APERTURE	Ø10
SURFACE QUALITY	20-10
TRANSMITTED WAVEFRONT	λ/4 @ 632.8nm
WAVELENGTH RANGE	200 - 3500nm

THIRD ANGLE PROJECTION		TITLE	A-BBO ROCHON POLARIZER	
ALL DIMS IN	mm			
DWG NO		68827		SHEET 1 OF 1