





NOTES:

1. SUBSTRATE: UV FUSED SILICA
2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (nm)	260
FULL WIDTH HALF MAX (FWHM) (nm)	10±2
MIN TRANSMISSION (%)	12
CLEAR APERTURE	Ø21.00
BEVEL	PROTECTIVE AS NEEDED

EO® Edmund Optics®



ALL DIMS IN

mm

TITLE

260nm, 10nm FWHM, 25mm DIA. FIRST SURFACE UV BANDPASS FILTER

DWG NO

11992

SHEET
1 OF 1