





- NOTES:
- 1. SUBSTRATE: UV FUSED SILICA
 - 2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




BANDPASS FILTER

	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (nm)	313
FULL WIDTH HALF MAX (FWHM) (nm)	10±2
MIN TRANSMISSION (%)	15
CLEAR APERTURE	Ø21.00
BEVEL	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	313nm, 10nm FWHM, 25mm DIA. FIRST SURFACE UV BANDPASS FILTER	
ALL DIMS IN	mm	DWG NO	11997	SHEET 1 OF 1