




NOTES:


1. SUBSTRATE: BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE):
S1 & S2: R(AVG) <1.0% @ 700 - 1150nm
3.  FINE GRIND SURFACE
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	4 - 6λ	4 - 6λ
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	45.00 x 45.00	45.00 x 45.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	50 x 50 x 3.3mm THICKNESS, NIR COATED, BOROFLOAT® WINDOW	
DWG NO	12194	SHEET 1 OF 1