




NOTES:

1. SUBSTRATE:
BOROFLOAT®
2. COATING (APPLY ACROSS COATING APERTURE)
S1: Multi-Layer DiElectric
T(AVG) ≥85% @ 425 - 675nm
R(AVG) ≥90% @ 750 - 1125nm
S2: NONE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®



THIRD ANGLE
PROJECTION

TITLE

45° Hot Mirror Mounted in C-Mount Cube

ALL DIMS IN

mm

DWG NO

62641

SHEET
1 OF 1

	S1	S2
SURFACE QUALITY	80-50	80-50