






FOCAL LENGTH (EFL): 15 ± 0,15
BACK FOCAL LENGTH (BFL): 10,66

1 BLACKENED SURFACE

SURFACE A			SURFACE B		SURFACE C	
Øe 9			Øe 9		Øe 9	
			CEMENT: NOA 61 OR EQUIVALENT			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 10mm Dia, x 15mm FL, VIS 0, Inked, Achromatic Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 63705INK	SHEET SIZE A4
						SHEET 1 OF 3



- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 10,04±0,01 CX Øe 9 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BaF10 670/472	R 7±0,007 CX Øe 9 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE


λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE
PROJECTION



ALL DIMS
IN:

mm



Edmund Optics®

TITLE


10mm Dia, x 15mm FL, VIS 0, Inked,
Achromatic Lens

DWG NO

637051NK

SHEET SIZE
A4

SHEET
2 OF 3



- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 7±0,007 CV Øe 9 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF10 728/284	R 80,71±0,081 CX Øe 9 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE		10mm Dia, x 15mm FL, VIS 0, Inked, Achromatic Lens		
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					DWG NO	63705INK		SHEET SIZE A4	SHEET 3 OF 3
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm					