



PART	PART #	MATERIAL
①	#46-213	Hoya ND-40
②	#56-353	Anodized Aluminum

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	FILTER SPECIFICATIONS
CLEAR APERTURE (mm)	> $\phi 22.00$
TRANSMISSION	T (AVG) > 40% @ 400 - 700 nm
OPTICAL DENSITY	0.4 $\pm$ 0.05
SURFACE QUALITY	80-50



ALL DIMS IN

mm

EO® **Edmund Optics®**

TITLE

0.4 OD, 22mm CA, C-Mount Absorptive ND
Filter

DWG NO

13018

SHEET
1 OF 1