



| PART | PART #  | MATERIAL          |
|------|---------|-------------------|
| ①    | #48-092 | Hoya ND-0.3       |
| ②    | #56-353 | Anodized Aluminum |

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                     | FILTER SPECIFICATIONS       |
|---------------------|-----------------------------|
| CLEAR APERTURE (mm) | > $\varnothing 22.00$       |
| TRANSMISSION        | T (AVG) > 1% @ 400 - 700 nm |
| OPTICAL DENSITY     | 2.0 $\pm$ 0.05              |
| SURFACE QUALITY     | 80-50                       |



ALL DIMS IN

mm



**Edmund Optics®**

TITLE

2.0 OD, 22mm CA, C-Mount Absorptive ND  
Filter

DWG NO

13024

SHEET  
1 OF 1