



NOTES:
1. RoHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	VALUE
DESIGN WAVELENGTH DWL (nm)	1064
INPUT DIAMETER (mm)	12.0 - 12.1mm (1/e ²)
WAVELENGTH RANGE (nm)	1020 - 1100

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

TITLE	1064nm Flat Top Beam Shaper πShaper 12_12_1064_HP		
DWG NO	15495	SHEET	1 OF 1