



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

NOTES:

1. SUBSTRATE: ISUZU ISK171  
DENSITY: 2.60g/cm³  
REFLECTION FACTOR: 0.92  
KNOOP HARDNESS: 517kg/mm²  
REFRACTIVE INDEX: 1.529nm
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
FUNCTION	HEAT ABSORBING
SURFACE QUALITY	60-40
CLEAR APERTURE	Ø11.25
BEVEL MAX FACE	PROTECTIVE AS NEEDED



ALL DIMS IN mm

**EO**® **Edmund Optics®**

TITLE

ISUZU ISK171, 12.5 Dia., HEAT ABSORBING  
COLORED GLASS FILTER

DWG NO

15703

SHEET  
1 OF 1