



NOTES:

1. SUBSTRATE: ISUZU ISK157
 DENSITY: 2.60g/cm³
 REFLECTION FACTOR: 0.92
 KNOOP HARDNESS: 481kg/mm²
 REFRACTIVE INDEX: 1.518nm
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
FUNCTION	HEAT ABSORBING
SURFACE QUALITY	60-40
CLEAR APERTURE	$\varnothing 45.00$
BEVEL MAX FACE	PROTECTIVE AS NEEDED



ALL DIMS IN mm

EO[®] Edmund Optics[®]

TITLE

ISUZU ISK157, 50 Dia., HEAT ABSORBING
COLORED GLASS FILTER

DWG NO

15712

SHEET
1 OF 1