
## PN: ST-212-Q-Y-A



INPUT PARAMETER	
Wavelength [nm]:	532
Required Beam Diameter [mm]:	7
Beam Mode (SM/MM):	Single Mode TEM00 with M^2<1.5

ELEMENT PARAMETER	
Element Type:	Window
Material:	Fused Silica
Element Size [mm]:	20
Clear Aperture [mm]:	17.5
Thickness [mm]:	3
Coating:	AR/AR coating

OUTPUT PARAMETER	
Output Shape:	Square
Full Angle at 1/e2 [mRad]:	0.50
Transfer Region [mRad]:	0.035
Transmission efficiency:	Close to 100%
Overall Efficiency:	~ 94%

Holo/Or can improve the performances of this item. Please send us your requirements