

NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) <0.25% @ 532nm R(ABS) <0.25% @ 1064nm R(AVG) <1.0% @ 500 - 1100nm



5. Rohs Compliant







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

\$1	\$2
PLANO	PLANO
60-40	60-40
Ø9.00	Ø9.00
PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED
	60-40 Ø9.00

		5	
THIRD ANGLE - PROJECTION		TITLE	
ALL DIMS IN	mm	DWG NO	133

Edmund Option	CS®
10mm DIA., 2mm THICK, YAG-BB, COATED, λ/4 N-BK7 WINDOW	ΑR
13310	SHEET 1 OF 1