



NOTES:

- 1. SUBSTRATE: UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: R(AVG) <0.5% @ 350 - 700nm
- 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN <5 ARCSEC

- 4. FINE GRIND SURFACE
- 5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	Ø40.00	Ø40.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	50mm DIA., 6mm THICK, VIS-EXT COATED, λ/10 FUSED SILICA WINDOW	
DWG NO	13346	SHEET 1 OF 1