

NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) <0.25% @ 532nm R(ABS) <0.25% @ 1064nm R(AVG) <1.0% @ 500 - 1100nm



5. Rohs Compliant





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| | \$1 | \$2 | | |
|---------------------|----------------------|----------------------|--|--|
| SHAPE | PLANO | PLANO | | |
| SURFACE QUALITY | 60-40 | 60-40 | | |
| CLEAR APERTURE (mm) | Ø45.72 | Ø45.72 | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | | |

| | | | Eamuna Option | S® |
|-----------------------------|------------------------|--------|---|-----------------|
| THIRD ANGLE _ PROJECTION | $\phi \Leftrightarrow$ | TITLE | 50.8mm DIA., 4mm THICK, YAG-BB, COATED, λ/4 N-BK7 WINDOW | ٩R |
| ALL DIMS IN | mm | DWG NO | 15794 | SHEET 1 OF 1 |

