






FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

1. SUBSTRATE:
SCHOTT NG4
2. OPTICAL DENSITY: 0.9
3. TRANSMISSION (%): 12.6% AVERAGE FROM 400-700nm



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG4, 0.9 OD, 50mm SQ., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16731	SHEET 1 OF 1