

NOTES:





1. SUBSTRATE: BOROFLOAT33
2. COATING

DURABILITY:  
 PHYSICAL: MIL-C-48497A, SECTION 3.4.1  
 ENVIRONMENTAL: MIL-STD-810F, SECTION 507.4

PERFORMANCE SPECIFICATIONS @ 0° AOI  
 T(AVG): ≥85% from 400 - 580nm  
 T(AVG): ≤1% from 625 - 775nm  
 CUT-OFF WAVELENGTH: T(ABS) = 50% @ 600nm ± 12nm

3. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**



SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø11.25	Ø11.25
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

**EO**® **Edmund Optics**®

TITLE	FILTER OD2 SHORTPASS 600nm 12.5mm		
DWG NO	15248	SHEET	1 OF 1