

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**





NOTES:

1. SUBSTRATE: BOROFLOAT33
2. COATING

DURABILITY:
PHYSICAL: MIL-C-48497A, SECTION 3.4.1
ENVIRONMENTAL: MIL-STD-810F, SECTION 507.4

PERFORMANCE SPECIFICATIONS @ 0° AOI
T(AVG): ≥85% from 400 - 630nm
T(AVG): ≤1% from 675 - 850nm
CUT-OFF WAVELENGTH: T(ABS) = 50% @ 650nm ± 13nm

3. ROHS COMPLIANT




SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø11.25	Ø11.25
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm

EO® **Edmund Optics**®

TITLE

FILTER OD2 SHORTPASS 650nm 12.5mm

DWG NO

15249

SHEET
1 OF 1