

NOTES:



- SUBSTRATE MATERIAL:
NITROCELLULOSE
- COATING (APPLY ACROSS COATING APERTURE)

S1: NONE


45% R @ 3000 - 5000nm @ 45° AOI
55% T @ 3000 - 5000nm @ 45° AOI

S2: NONE

- ROHS : COMPLIANT



SECTION A-A



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



| | S1 | S2 |
|-----------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 40-20 | 40-20 |
| CLEAR APERTURE | Ø76.20 | Ø76.20 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION

ALL DIMS IN mm

| | | | |
|--------|---|-------|--------|
| TITLE | 76.2mm Clear Aperture 45R/55T, Infrared Pellicle Beamsplitter | | |
| DWG NO | 19283 | SHEET | 1 OF 1 |