





NOTES:

1. SUBSTRATE: Hoya UV30N



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                        | VALUE                |
|------------------------|----------------------|
| SHAPE                  | PLANO                |
| $\Delta\lambda$        | <40                  |
| TH (%)                 | >85                  |
| CUT-ON WAVELENGTH (nm) | 300±7                |
| SURFACE QUALITY        | 60-40                |
| WAVELENGTH             | UV                   |
| BEVEL                  | PROTECTIVE AS NEEDED |

**EO**® Edmund Optics®



|             |    |       |   |        |       |                 |
|-------------|----|-------|---|--------|-------|-----------------|
| ALL DIMS IN | mm | TITLE | Hoya UV30N (300nm), 25.4mm Dia., 1mm Thick, Colored Glass Longpass Filter | DWG NO | 18801 | SHEET<br>1 OF 1 |
|-------------|----|-------|---|--------|-------|-----------------|