




**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                                 | VALUE        |
|---------------------------------|--------------|
| SHAPE                           | PLANO        |
| CENTER WAVELENGTH (nm)          | 630          |
| FULL WIDTH HALF MAX (FWHM) (nm) | 120          |
| MINIMUM TRANSMISSION (%)        | >70          |
| TRANSMITTED WAVEFRONT, RMS      | $\lambda/4$  |
| PARALLELISM (arcsec)            | 30 or better |



ALL DIMS IN

mm



TITLE

Filter Bandpass Johnson/Bessel-R 25mm

DWG NO

21124

SHEET  
1 OF 1