

NOTES:



1. SUBSTRATE:
FUSED SILICA

2. ROHS COMPLIANT

3. COATED SURFACE

S1: Ravg >96% @ 700 - 2000nm
Ravg >96% @ 2000 - 10,000nm

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 |
|------------------------|----------------|----------------|
| WAVELENGTH RANGE (nm) | 700-10000 | 700-10000 |
| ROOF ACCURACY (ARCSEC) | 90 ± 10 | 90 ± 10 |
| SURFACE QUALITY | 20-10 | 20-10 |
| CLEAR APERTURE | 90% | 90% |
| COATING | PROTECTED GOLD | PROTECTED GOLD |

THIRD ANGLE PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE

TECHSPEC Unmounted Protected Gold
Hollow Retroreflector

DWG NO

17547

SHEET
1 OF 1