



NOTES:

- 1. SUBSTRATE:  
Fused Silica
- 2. PARALLELISM:  
SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO <3 ARCMIN
- 3. COATING:  
S1 & S2: NONE

4. FINE GRIND SURFACE

5. ROHS COMPLIANT




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	1λ	1λ
CLEAR APERTURE	Ø43.18	Ø43.18
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE  
PROJECTION



ALL DIMS IN

mm

**EO**® **Edmund Optics®**

TITLE

50.8mm Dia., 3mm Thick, Uncoated, ISP  
Optics IR Fused Silica Window

DWG NO

24588

SHEET  
80 OF 175