


- NOTES:
- 1. SUBSTRATE:
GERMANIUM
 - 2. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (μm)	12.10 ±0.04
FULL WIDTH HALF MAX (FWHM) (μm)	0.50 ±0.05
MIN TRANSMISSION (%)	>80%
CLEAR APERTURE	Ø 22.00
BEVEL	PROTECTED AS NEEDED

<div><div>EO[®]</div><div>Edmund Optics[®]</div></div>			
THIRD ANGLE PROJECTION		TITLE	12.10μm CWL, 25.0mm Diameter, 0.50μm FWHM, IR Bandpass Filter
ALL DIMS IN	mm	DWG NO	25723
			SHEET 4 OF 4