



NOTES:

1. SUBSTRATE:
BOROFLOAT®
3. COATING
S1: Protected Gold (700-10000nm)
R(AVG) >96% @ 700 - 2000nm
R(AVG) >96% @ 2000 - 10,000nm

S2:NONE
3. FINE GRIND SURFACE (ADD INK NOTE AS NEEDED)
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			<div><div><div>EO®</div><div>Edmund Optics®</div></div><div>12.7mm Dia. Protected Gold, λ/4 Mirror</div></div>		
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION		TITLE		
SURFACE QUALITY	60 - 40	COMMERCIAL POLISH					
CLEAR APERTURE	Ø11.43	N/A					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	25732	SHEET 3 OF 12