

NOTES:

1. SUBSTRATE:
BOROFLOAT®




3. COATING

S1: Protected Silver (450-10000nm)
R(AVG) >98% @ 450 - 2000nm
R(AVG) >98% @ 2000 - 10,000nm

S2:NONE

3. FINE GRIND SURFACE (ADD INK NOTE AS NEEDED)

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60 - 40	COMMERCIAL POLISH
CLEAR APERTURE	∅ 22.86	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN

mm

EO® Edmund Optics®

TITLE

25.4mm Dia. Protected Silver, λ/4 Mirror

DWG NO

25737

SHEET
8 OF 12