




NOTES:

1. SUBSTRATE:
BOROFLOAT®
3. COATING
S1: Protected Gold (700-10000nm)
R(AVG) >96% @ 700 - 2000nm
R(AVG) >96% @ 2000 - 10,000nm

S2:NONE
3. FINE GRIND SURFACE (ADD INK NOTE AS NEEDED)
4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60 - 40	COMMERCIAL POLISH
CLEAR APERTURE	Ø 45.72	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 Edmund Optics®

TITLE	50.8mm Dia. Protected Gold, λ/4 Mirror	
DWG NO	25740	SHEET 11 OF 12