

In order to provide more accurate inventory information, please select your shipping country.

Sélectionner votre Pays/Région: European Union

SUBMIT

# Platine a Roulement a Billes sans Trous de Passage, Entraînement micrometrique Anglais, Déplacement de 1"



32mm/1.25" Side drive stage and its X-Y-Z configuration

Stock **#37-955** [CONTACT](#)



1



€521,00

AJOUTER AU PANIER

Qté 1+

€521,00

Prix sur Quantité

[Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Type de Mouvement:  
Linear (X)

Guide System:  
Ball Bearing

Mécanisme:  
English Micrometer

Position de la Vis:  
Side Drive

|                                               |
|-----------------------------------------------|
| Type:<br>English                              |
| Taille de Plateau (mm):<br>44.4 x 44.4        |
| Course (pouces):<br>1                         |
| Longueur (mm):<br>55.37                       |
| Construction:<br>Aluminium Stage              |
| Graduations (pouces):<br>0.001                |
| Hauteur (pouces):<br>0.75                     |
| Hauteur (mm):<br>19.1                         |
| Capacité de Charge, Normale (lbs):<br>25      |
| Remarque:<br>Solid Top                        |
| Taille de Plateau (pouces):<br>1.75 x 1.75    |
| Précision (pouces):<br>0.00008/inch of travel |
| Poids (lbs):<br>0.5                           |
| Thrust Capacity, T <sub>a</sub> (lbs):<br>10  |
| Thrust Capacity, T <sub>b</sub> (lbs):<br>5   |

Conformité réglementaire

|                                                          |
|----------------------------------------------------------|
| RoHS 2015:<br><a href="#">Conforme</a>                   |
| Certificate of Conformance:<br><a href="#">Visionner</a> |