

In order to provide more accurate inventory information, please select your shipping country:

Sélectionner votre Pays/Région: European Union

SUBMIT

Platine a Roulement a Billes sans Trous de Passage, Entraînement micrométrique
Métrique, Déplacement de 25 mm



32mm/1.25" Side drive stage and its X-Y-Z configuration

Stock #37-956 3-4 JOURS



1



€521,00

AJOUTER AU PANIER

Qté 1+

€521,00

Prix sur Quantité

[Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Type de Mouvement:
Linear (X)

Guide System:
Ball Bearing

Mécanisme:
Metric Micrometer

Position de la Vis:
Side Drive

Type: English
Taille de Plateau (mm): 44.4 x 44.4
Course (mm): 25
Longueur (mm): 55.37
Construction: Aluminium Stage
Graduations (mm): 0.01
Hauteur (pouces): 0.75
Hauteur (mm): 19.1
Capacité de Charge, Normale (lbs): 25
Remarque: Solid Top
Taille de Plateau (pouces): 1.75 x 1.75
Précision (pouces): 0.00008/inch of travel
Poids (lbs): 0.5
Thrust Capacity, T _a (lbs): 10
Thrust Capacity, T _b (lbs): 5

Conformité réglementaire

RoHS 2015: Conforme
Certificate of Conformance: Visionner