

In order to provide more accurate inventory information, please select your shipping country.

Sélectionner votre Pays/Région: European Union

SUBMIT

Platine a Roulement a Billes sans Trous de Passage, Entraînement micrométrique Métrique, Déplacement de 25 mm



Solid Top Stage



Stock #33-487 3-4 JOURS



1



€854,00

AJOUTER AU PANIER

Qté 1+

€854,00

Prix sur Quantité

[Demande de Devis](#)

Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Type de Mouvement:
Linear (X)

Guide System:
Ball Bearing

Mécanisme:

Metric Micrometer
Position de la Vis: Center Drive
Type: English
Taille de Plateau (mm): 127 x 127
Course (mm): 25
Construction: Aluminium Stage
Graduations (mm): 0.01
Hauteur (pouces): 1.00
Hauteur (mm): 25.4
Capacité de Charge, Normale (lbs): 105
Remarque: Solid Top
Taille de Plateau (pouces): 5.00 x 5.00
Précision (pouces): 0.00008/inch of travel
Poids (lbs): 2.7
Thrust Capacity, T_a (lbs): 30
Thrust Capacity, T_b (lbs): 2.5

Conformité réglementaire

RoHS 2015: Conforme
Certificate of Conformance: Visionner