

[Afficher tous les 18 produits de la même famille.](#)

4" x 4", White, UltraSeal Washdown Backlight

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Backlights

Stock **#18-608** [CONTACT](#)

- 1 +

€1.129,00

AJOUTER AU PANIER

Qté 1+

€1.129,00

Prix sur Quantité

[Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Couleur:
White

Tension d'Entrée (V):
24V

Numéro de Modèle:
BL245-0404WHIIC

Température d'Utilisation (°C):
0 - 60

Dimensions (mm): 122.2 x 122.2 x 24.0
Poids (g): 386
Durée de Vie LED (heures): 50000
Alimentation d'Énergie: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Zone Active (inches): 4 x 4
Type d'Éclairage: LED Illuminator
Remarque: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Fabricant: Advanced Illumination
Géométrie: Backlight
Mode d'Éclairage: Constant
Norme Environnementale: IP69K
Courant d'entrée minimum: 0.48A

Conformité réglementaire

RoHS 2015: Dispensé
Certificate of Conformance: Visionner
Reach 233: Contains SVHC(s)