

6" x 6", Red 660nm, UltraSeal Washdown Backlight

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Backlights

Stock #18-619 3-4 JOURS

- 1 +

€1.345,00

AJOUTER AU PANIER

Qté 1+

€1.345,00

Prix sur Quantité

[Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Couleur:
Red

Tension d'Entrée (V):
24V

Numéro de Modèle:
BL245-06066601C

Température d'Utilisation (°C):
0 - 60

Dimensions (mm): 173.0 x 173.0 x 24.0
Longueur d'Onde (nm): 660.00
Poids (g): 698
Durée de Vie LED (heures): 50000
Alimentation d'Énergie: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Zone Active (inches): 6 x 6
Type d'Éclairage: LED Illuminator
Remarque: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Fabricant: Advanced Illumination
Géométrie: Backlight
Mode d'Éclairage: Constant
Norme Environnementale: IP69K
Courant d'entrée minimum: 1.08A

Conformité réglementaire

RoHS 2015: Dispensé
Certificate of Conformance: Visionner
Reach 233: Contains SVHC(s)