

[Afficher tous les 12 produits de la même famille.](#)

625nm 150mm Compact Light w/ Multi-Drive™



150mm Compact Light



Stock #23-939 **1 In Stock**

⊖ 1 ⊕ €710⁰⁰

AJOUTER AU PANIER

Prix sur Quantité

Qté 1+	€710,00 prix unitaire
Need More?	Demande de Devis

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Caractéristiques du produit

JWL150-MD-625 **Numéro de Modèle:**

LED Illuminator **Type d'Éclairage:**

Smart Vision Lights LLC **Fabricant:**

Ring Light	Géométrie:
Constant or Strobed	Mode d'Éclairage:
Propriétés physiques et mécaniques	
158.75 W x 84.25 H x 40.18 D (58.15 D Including Connector)	Dimensions (mm):
589.67	Poids (g):
65.38W x 65.38W	Zone Active (mm):
Propriétés optiques	
Red	Couleur:
625	Longueur d'Onde (nm):
500 - 2,000	Distance de Travail (mm):
Electrical	
30 - ∞	Strobe Duration (µs):
Connectivité matérielle & interfaçage	
5-pin M12 connector	Connecteur:
24 VDC ± 5%	Tension d'Entrée (V):
Filetage & montage	
T-Slot for M6 Nut	Monture:
Environnement & durabilité	
-10° to +40°	Température d'Utilisation (°C):
IP65	Norme Environnementale:
Conformité réglementaire	
Visionner	Certificate of Conformance:

Description produit

- Direct Connect and Control via Camera's Trigger Output
- Built-In Multi-Drive™ Technology
- T-Slots for Mounting

Smart Vision Lights Compact Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Multi-Drive™ technology, which offers both continuous operation and OverDrive™ mode, delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10mS. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Vision Lights Illumination products offer an industry-leading 10-year limited warranty.