

[Afficher tous les 12 produits de la même famille.](#)

## 625nm 225mm Compact Light w/ Multi-Drive™



225mm Compact Light



Stock **#23-945** 1 In Stock

-

1

+

€1.395<sup>00</sup>

AJOUTER AU PANIER

| Prix sur Quantité |                                  |
|-------------------|----------------------------------|
| Qté 1+            | €1.395,00 prix unitaire          |
| Need More?        | <a href="#">Demande de Devis</a> |

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

| Caractéristiques du produit |                   |
|-----------------------------|-------------------|
| JWL225-MD-625               | Numéro de Modèle: |
| LED Illuminator             | Type d'Éclairage: |
| Smart Vision Lights LLC     | Fabricant:        |

|                                                   |                                 |
|---------------------------------------------------|---------------------------------|
| Ring Light                                        | Géométrie:                      |
| Constant or Strobed                               | Mode d'Éclairage:               |
| Propriétés physiques et mécaniques                |                                 |
| 230 W x 142 H x 45D (60.40 D Including Connector) | Dimensions (mm):                |
| 1496.85                                           | Poids (g):                      |
| 144.50W x 56.5H                                   | Zone Active (mm):               |
| Propriétés optiques                               |                                 |
| Red                                               | Couleur:                        |
| 625                                               | Longueur d'Onde (nm):           |
| 500 - 2,000                                       | Distance de Travail (mm):       |
| Electrical                                        |                                 |
| 30 - ∞                                            | Strobe Duration (µs):           |
| Connectivité matérielle & interfaçage             |                                 |
| 5-pin M12 connector                               | Connecteur:                     |
| 24 VDC ± 5%                                       | Tension d'Entrée (V):           |
| Filetage & montage                                |                                 |
| T-Slot for M6 Nut                                 | Monture:                        |
| Environnement & durabilité                        |                                 |
| -10° to +40°                                      | Température d'Utilisation (°C): |
| IP65                                              | Norme Environnementale:         |
| Conformité réglementaire                          |                                 |
| <a href="#">Visionner</a>                         | Certificate of Conformance:     |

## Description produit

- Direct Connect and Control via Camera's Trigger Output
- Built-In Multi-Drive™ Technology
- T-Slots for Mounting

Smart Vision Lights Compact Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Multi-Drive™ technology, which offers both continuous operation and OverDrive™ mode, delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10mS. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Visions Lights Illumination products offer an industry-leading 10-year limited warranty.