

In order to provide more accurate inventory information, please select your shipping country:

Sélectionner votre Pays/Région: European Union ▼

SUBMIT



Advanced Illumination Side-Fired Collimated LED Backlight

Stock #36-475 3-4 JOURS



1



€1.345,00

AJOUTER AU PANIER

Qté 1+

€1.345,00

Prix sur Quantité

[Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Couleur:
Red

Numéro de Modèle:
CX0808-625IC

Température d'Utilisation (°C):
0 - 60

Dimensions (mm):
268.2 L x 268.2 W x 19.1 T

Durée de Vie LED (heures): 50,000
Alimentation d'Énergie: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Zone Active (inches): 8 x 8
Type d'Éclairage: LED Illuminator
Remarque: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Fabricant: Advanced Illumination
Géométrie: Backlight
Mode d'Éclairage: Constant

Conformité réglementaire

RoHS 2015: Conforme
Certificate of Conformance: Visionner
Reach 233: Contains SVHC(s)