
PN: DS-002-A-Y-A



INPUT PARAMETER	
Wavelength [nm]:	10600
Beam Mode (SM/MM):	SM or MM
Minimum Beam Diameter [mm]:	>1.35

ELEMENT PARAMETER		
Element Type:	Window	
Material:	ZnSe	
Element Size [mm]:	27.94	
Clear Aperture [mm]:	25.1	
Thickness [mm]:	3	
Coating:	AR/AR coating	

OUTPUT PARAMETER	
Number of Spots:	2
Separation Angle [deg]:	2.70
Of [deg]:	2.70
Transmission efficiency:	Close to 100%
Overall Efficiency:	~ 79%
Uniformity (Contrast) [%]:	<1%
Zero-Order relative to the incident beam [%]:	<1

Holo/Or can improve the performances of this item. Please send us your requirements